

# 21561154055 Cut Sheet



Pfannenberg PYRA series Xenon tube industrial signal beacon, 212 x 144 x 157mm, amber, selectable flashing strobe, IP66, NEMA 4/4X, surface mount, 115 VAC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/21561154055>

## Technical Specifications

|                             |                            |
|-----------------------------|----------------------------|
| <b>Brand</b>                | Pfannenberg                |
| <b>Item</b>                 | Industrial signal beacon   |
| <b>Bulb Type</b>            | Xenon tube                 |
| <b>Series</b>               | PYRA                       |
| <b>Operator Size</b>        | 212 x 144 x 157mm          |
| <b>Operator Color</b>       | Amber                      |
| <b>Light Color(s)</b>       | Amber                      |
| <b>Light Function</b>       | Selectable flashing strobe |
| <b>IP Rating</b>            | IP66                       |
| <b>NEMA Rating</b>          | 4/4X                       |
| <b>Mounting</b>             | Surface                    |
| <b>Touch to Acknowledge</b> | No                         |
| <b>Voltage Rating</b>       | 115 VAC                    |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E189090                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/21561154055.pdf>  
See store item page for other formats.