

# 265038UNC Cut Sheet

RUKO machine tap, 3/8-16 UNC, square shank per DIN 10, reinforced for through threads, 5% cobalt high-speed steel (HSSE-Co5), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/265038UNC>

## Technical Specifications

<b>Brand</b>	RUKO
<b>Item</b>	Machine tap
<b>Thread</b>	3/8-16 UNC per ANSI/ASME B1.1
<b>Thread Length</b>	0.87in
<b>Overall Length</b>	3.9in (99mm)
<b>Tap Drill Size</b>	5/16in
<b>Shank</b>	Square shank per DIN 10, reinforced for through threads
<b>Material</b>	5% cobalt high-speed steel (HSSE-Co5)
<b>Finish</b>	Bright
<b>For Use On</b>	Stainless steel, brass, steel, aluminum, bronze, plastic and cast iron
<b>Application</b>	Thread making

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>