

AM1-A0-1H Cut Sheet



Micro Detectors inductive proximity sensor, tubular, 12mm diameter x 75mm body, nickel-plated brass housing, NPN/PNP, N.O. output, 2mm sensing distance, flush, 1.5 kHz switching frequency, IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AM1-A0-1H>

Technical Specifications

Brand	Micro Detectors
Item	Proximity sensor
Sensor Type	Inductive
Application	Standard duty
Shape	Tubular
Housing Size	12mm diameter x 75mm body
Housing Material	Nickel-plated brass
Barrel Type	Threaded
Sensing Method	Standard sensing
Adjustable	No
Number of Wires	2
Switching Output	NPN/PNP
Operation Mode	N.O. output

Sensing Distance	2mm
Mounting Type	Flush
IO-Link Compatible	No
Switching Frequency	1.5 kHz
Operating Voltage	10-30 VDC
Operating Temperature	-25 to 70c
Weld Field Immune	No
Chip Immune	No
IP Rating	IP67
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	Not Applicable
UL Recognized File #	E130644
UL Hazardous File #	Not Applicable
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AM1-A0-1H.pdf>
See store item page for other formats.