

AM1-A0-2A Cut Sheet



Micro Detectors inductive proximity sensor, tubular, 12mm diameter x 60mm body, nickel-plated brass housing, NPN/PNP, N.O. output, 4mm sensing distance, non-flush, 1.5 kHz switching frequency, IP67, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AM1-A0-2A>

Technical Specifications

Brand	Micro Detectors	Sensing Distance	4mm
Item	Proximity sensor	Mounting Type	Non-flush
Sensor Type	Inductive	IO-Link Compatible	No
Application	Standard duty	Switching Frequency	1.5 kHz
Shape	Tubular	Operating Voltage	10-30 VDC
Housing Size	12mm diameter x 60mm body	Operating Temperature	-25 to 70c
Housing Material	Nickel-plated brass	Weld Field Immune	No
Barrel Type	Threaded	Chip Immune	No
Sensing Method	Standard sensing	IP Rating	IP67
Adjustable	No	Connection	Pigtail
Number of Wires	2	Conductor Size	24 AWG
Switching Output	NPN/PNP	Cable Length	6.5ft/2m
Operation Mode	N.O. output	Includes	Mounting hardware

Agency Approvals

UL Listed File #	Not Applicable
UL Recognized File #	E130644
UL Hazardous File #	Not Applicable
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document