

# 27691 Cut Sheet



Halex fitting, liquid-tight, nylon, 90-degree, 1/2in trade size, compression conduit connection, insulation, gray. Package of 1. For use with NM-Type B electrical conduit. Sealing washer and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/27691>

## Technical Specifications

|                           |                |
|---------------------------|----------------|
| Brand                     | Halex          |
| Item                      | Fitting        |
| Liquid-tight              | Yes            |
| Fitting Type              | 90-degree      |
| Material                  | Nylon          |
| Trade Size                | 1/2in          |
| Conduit Connection Method | Compression    |
| Box Connection Type       | 1/2in male NPT |
| Insulation                | Yes            |

|                                                          |                              |
|----------------------------------------------------------|------------------------------|
| Color                                                    | Gray                         |
| Knockout Size                                            | 1/2in                        |
| Liquid-tight Non-metallic Conduit Type B (NM) Trade Size | 1/2in                        |
| Quantity per Pack                                        | 1                            |
| For Use With                                             | NM-Type B electrical conduit |
| Includes                                                 | Sealing washer and locknut   |
| Applicable Standards                                     | UL 514B Listed               |

## Agency Approvals

|                  |                                                                     |
|------------------|---------------------------------------------------------------------|
| UL Listed File # | E30248                                                              |
| RoHS Status      | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH         | <a href="#">View EU REACH document</a>                              |
| Other            | <a href="#">RoHS Statement</a>                                      |