

38620 Cut Sheet



FTG enclosed terminal block, finger-safe, 225A, 1-pole, line side:
1 opening accepts 250 kcmil to 2 AWG, load side: 2 openings
accept 2 AWG to 14 AWG & 5 openings accept 6 AWG to 14 AWG
& 4 openings accept 8 AWG to 14 AWG, panel or 35mm DIN rail
mount.

For complete product information, please see this item on our
store at the following link:



<https://www.automationdirect.com/pn/38620>

Technical Specifications

Brand	FTG
Item	Terminal block
Terminal Block Type	Enclosed
Modular	No
Finger-safe	Yes
Amperage Rating	225A
Number of Poles	1
Line Side Openings	1 opening accepts 250 kcmil to 2 AWG
Load Side Openings	2 openings accept 2 AWG to 14 AWG & 5 openings accept 6 AWG to 14 AWG & 4 openings accept 8 AWG to 14 AWG
Mounting	Panel or 35mm DIN rail
SCCR Rating	10kA SCCR
UL Rating	UL 1059 recognized
IP Rating	IP20

Agency Approvals

UL Recognized File #	E98082
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
[https://cdn.automationdirect.com
/static/drawings/2d/38620.pdf](https://cdn.automationdirect.com/static/drawings/2d/38620.pdf)
See store item page for other formats.