

4362 Cut Sheet



Marathon standard efficiency AC induction motor, general purpose, 1/4hp, 1-phase, 115 VAC, 1800rpm, ODP, 48 frame, rolled steel, rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/4362>

Technical Specifications

Brand	Marathon	Shaft Type	Round with square key
Item	Motor	Shaft Diameter	1/2in
Efficiency Group	Standard efficiency	Shaft Material	1117 steel
Efficiency	52.5	Motor Frame	48
Voltage Type	AC	Frame Material	Rolled steel
Motor Type	Induction	Electrically Reversible	Yes
Motor Application	General purpose	Insulation Class	Class B
Horsepower Rating	1/4hp	IP Rating	IP22
Number of Phases	1	Service Factor	1.35
Voltage Rating	115 VAC	Integrated Brake	No
Synchronous Speed	1800rpm	Junction Box Orientation	F1
Nameplate RPM	1725rpm	Mounting	Rigid base
Overload Type	Automatic	Mounting Orientation	Any
Enclosure Type	ODP	Manufacturer Part Number	5KH39QN9686X

Agency Approvals

UL Listed File #	None
UL Recognized File #	E46035
UL Hazardous File #	None
CE	None
CSA File #	236833
RoHS Status	No
EU REACH	View EU REACH document