

# 6105313 Cut Sheet



Seifert SoliTherm thermoelectric cooler, 340 BTU/H, 120 VAC operating voltage, 304 stainless steel housing, filter-free, recessed mount. For use with NEMA 4/4X/12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/6105313>

## Technical Specifications

|                          |                       |
|--------------------------|-----------------------|
| Brand                    | Seifert               |
| Series                   | SoliTherm             |
| Item                     | Thermoelectric cooler |
| Nominal Cooling Capacity | 340 BTU/H             |
| Operating Voltage        | 120 VAC               |
| Frequency                | 50/60 Hz              |
| Running Current          | 1.1A                  |
| Height                   | 11.02in               |

|                  |                         |
|------------------|-------------------------|
| Width            | 13.78in                 |
| Depth            | 7.2in                   |
| Mounting         | Recessed                |
| Filter-Free      | Yes                     |
| Housing Material | 304 stainless steel     |
| IP Rating        | IP66                    |
| For Use With     | NEMA 4/4X/12 enclosures |
| Includes         | Mounting hardware       |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | SA32278                                |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/6105313.pdf>  
See store item page for other formats.