

# APDB-16-500-1 Cut Sheet



Penn-Union open power distribution block, finger-safe, 380A, 1-pole, line side: 1 openings accept 500 MCM to 4 AWG Cu/AL, load side: 6 openings accept 2/0 AWG to 14 AWG Cu/AL, DIN rail or panel mount, UL 1953 listed.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/APDB-16-500-1>

## Technical Specifications

<b>Brand</b>	Penn-Union
<b>Item</b>	Power distribution block
<b>Terminal Block Type</b>	Open
<b>Modular</b>	Yes
<b>Finger-safe</b>	Yes
<b>Amperage Rating</b>	380A
<b>Number of Poles</b>	1

<b>Line Side Openings</b>	1 openings accept 500 MCM to 4 AWG Cu/AL
<b>Load Side Openings</b>	6 openings accept 2/0 AWG to 14 AWG Cu/AL
<b>Mounting</b>	DIN rail or panel
<b>SCCR Rating</b>	100kA SCCR
<b>UL Rating</b>	UL 1953 listed
<b>IP Rating</b>	IP20
<b>Additional Information</b>	Suitable for branch and feeder circuits

## Agency Approvals

<b>UL Listed File #</b>	E534364
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/APDB-16-500-1.pdf>  
See store item page for other formats.