9002/22-158-200-001 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

R. STAHL intrinsically safe Zener barrier, common usage: 11V pulse trains, 24 VDC operating voltage, screw terminals.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/9002/22-158-200-001

Technical Specifications

Brand	R. STAHL
Item	Barrier
Barrier Type	Zener
Intrinsically Safe	Yes
Barrier Common Usage	11V pulse trains
Maximum Voltage	15.8 VDC
Maximum Current	200 mA

Maximum Power	395 mW
Operating Voltage	24 VDC
Housing Material	Polyamide
Mounting	35mm DIN rail
Connection	Screw terminals
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E81680
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	FM Approval and UL Control Drawing

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/9002_22-158-200-001.pdf
See store item page for other formats.