

APS25-8S-E-D Cut Sheet



Koyo inductive proximity sensor, rectangular, 8 x 26.5 x 7.4mm body, polycarbonate housing, top sensing, NPN, N.O. output, 2.5mm sensing distance, non-flush, 500 Hz switching frequency, IP67, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/APS25-8S-E-D>

Technical Specifications

Brand	Koyo	Sensing Distance	2.5mm
Item	Proximity sensor	Mounting Type	Non-flush
Sensor Type	Inductive	IO-Link Compatible	No
Application	Standard duty and small space	Switching Frequency	500 Hz
Shape	Rectangular	Operating Voltage	10-30 VDC
Housing Size	8 x 26.5 x 7.4mm body	Operating Temperature	-10 to 50C
Housing Material	Polycarbonate	Weld Field Immune	No
Sensing Face	Top sensing	Chip Immune	No
Sensing Method	Standard sensing	IP Rating	IP67
Adjustable	No	Connection	Pigtail
Number of Wires	3	Conductor Size	26 AWG
Switching Output	NPN	Cable Length	6.5ft/2m
Operation Mode	N.O. output	Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	E198343
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document