

# 9146-10-11-12S Cut Sheet



STAHL ISpac intrinsically safe frequency transmitter isolator, (1) 0.001 Hz to 20 kHz input, (1) 0-20 mA or 4-20 mA and (2) N.O./N.C. configurable output, 24 VDC operating voltage, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9146-10-11-12S>

## Technical Specifications

<b>Brand</b>	STAHL
<b>Series</b>	ISpac
<b>Item</b>	Isolator
<b>Isolator Type</b>	Frequency transmitter
<b>Intrinsically Safe</b>	Yes
<b>Input</b>	(1) 0.001 Hz to 20 kHz
<b>Output</b>	(1) 0-20 mA or 4-20 mA and (2) N.O./N.C. configurable
<b>Maximum Voltage</b>	10.5 VDC

<b>Maximum Current</b>	23.4 mA
<b>Maximum Power</b>	61.4 mW
<b>Operating Voltage</b>	24 VDC
<b>Housing Material</b>	Polyamide
<b>Mounting</b>	35mm DIN rail
<b>Connection</b>	Screw terminals
<b>Application</b>	Hazardous location rated
<b>Manufacturer Part Number</b>	9146/10-11-12s

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">FM Approval</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/9146-10-11-12S.pdf>  
See store item page for other formats.