


# 9270-21-17-14S Cut Sheet



STAHL intrinsically safe digital input isolator, (2) NAMUR sensors or (2) dry contacts input, (2) N.O. contacts output, 24 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9270-21-17-14S>

## Technical Specifications

|                               |  |
|-------------------------------|--|
| <b>Brand</b>                  | STAHL                                    |
| <b>Item</b>                   | Isolator                                 |
| <b>Isolator Type</b>          | Digital input                            |
| <b>Intrinsically Safe</b>     | Yes                                      |
| <b>Input</b>                  | (2) NAMUR sensors or (2) dry contacts    |
| <b>Output</b>                 | (2) N.O. contacts                        |
| <b>Maximum Voltage</b>        | 9.6 VDC                                  |
| <b>Maximum Current</b>        | 10 mA                                    |
| <b>Maximum Power</b>          | 25 mW                                    |
| <b>Operating Voltage</b>      | 24 VDC                                   |
| <b>Housing Material</b>       | Polyamide                                |
| <b>Mounting</b>               | 35mm DIN rail                            |
| <b>Connection</b>             | Screw terminals                          |
| <b>Application</b>            | Hazardous location rated                 |
| <b>Additional Information</b> | Manufacturer part number: 9270/21-17-14s |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E81680                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |