

# AT1-A0-1H Cut Sheet



Micro Detectors inductive proximity sensor, tubular, 30mm diameter x 60mm body, nickel-plated brass housing, NPN/PNP, N.O. output, 10mm sensing distance, flush, 150 Hz switching frequency, IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AT1-A0-1H>

## Technical Specifications

Brand	Micro Detectors	Sensing Distance	10mm
Item	Proximity sensor	Mounting Type	Flush
Sensor Type	Inductive	IO-Link Compatible	No
Application	Standard duty	Switching Frequency	150 Hz
Shape	Tubular	Operating Voltage	10-30 VDC
Housing Size	30mm diameter x 60mm body	Operating Temperature	-25 to 70c
Housing Material	Nickel-plated brass	Weld Field Immune	No
Barrel Type	Threaded	Chip Immune	No
Sensing Method	Standard sensing	IP Rating	IP67
Adjustable	No	Connection	4-pin M12 quick-disconnect
Number of Wires	2	Includes	Mounting hardware
Switching Output	NPN/PNP	Additional Information	Purchase cable separately
Operation Mode	N.O. output		

## Agency Approvals

UL Listed File #	Not Applicable
UL Recognized File #	E130644
UL Hazardous File #	Not Applicable
CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>