

96200005 Cut Sheet



LS Electric high-precision planetary gearbox, 10:1 ratio, inline, 16mm diameter output shaft, nominal output torque 42 N-m (372 lb-in), 1-stage, 60mm frame. For use with FBL series 100W, 200W and 400W motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/96200005>

Technical Specifications

Brand	LS Electric
Item	Gearbox
Application	High-precision
Gearbox Type	Planetary
Gear Ratio	10:1
Output Configuration	Inline
Gearbox Output Shaft Diameter	16mm
Nominal Output Torque	Nominal output torque 42 N-m (372 lb-in)
Number of Stages	1
Frame	60mm
For Use With	FBL series 100W, 200W and 400W motors
Includes	Input adapter bushing, motor mounting hardware and output shaft key
Manufacturer Part Number	MSS0601A-010KS-B3110103C14

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement