

96200005 Cut Sheet



LS Electric high-precision planetary gearbox, 10:1 ratio, inline, 16mm diameter output shaft, nominal output torque 42 N-m (372 lb-in), 1-stage, 60mm frame. For use with FBL series 100W-400W motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/96200005>

Technical Specifications

| | |
|-------------------------------|----------------|
| Brand | LS Electric |
| Item | Gearbox |
| Application | High-precision |
| Gearbox Type | Planetary |
| Gear Ratio | 10:1 |
| Output Configuration | Inline |
| Gearbox Output Shaft Diameter | 16mm |

| | |
|--------------------------|---|
| Nominal Output Torque | Nominal output torque 42 N-m (372 lb-in) |
| Number of Stages | 1 |
| Frame | 60mm |
| For Use With | FBL series 100W, 200W and 400W motors |
| Includes | Input adapter bushing, motor mounting hardware and output shaft key |
| Manufacturer Part Number | MSS0601A-010KS-B3110103C14 |

Agency Approvals

| | |
|----------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/96200005.pdf>
See store item page for other formats.