

A1491607-1 Cut Sheet



LUTZE SUPERFLEX continuous flexing control cable, shielded, 7 conductors (includes ground), 16 AWG (1.50mm²), bare copper, TPE conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A1491607-1>

Technical Specifications

Brand	LUTZE	Conductor Insulation Color	Black with white numbers and green/yellow ground
Item	Cable	Shielding	Shielded
Series	SUPERFLEX	Jacket Material	PVC
Wire/Cable Type	Control	Jacket Color	Gray
UL Wire/Cable Type	AWM	Nominal Overall Cable Diameter	0.488in
Applicable Standards	UL 2586	Bulk Length	Cut to length
Application	Automation	Package Type	1 to 50ft = Coil, 51 to 165ft = 14 x 7in Reel, 166 to 235ft = 14 x 10in Reel, 236 to 360ft = 16 x 10in Reel, 361 to 500ft = 18 x 10in Reel, 501 to 650ft = 18 x 13in Reel, 651 to 1460ft = 24 x 17in Wooden Reel, 1461 to 2335ft = 30 x 17in Wooden Reel, 2336 to 3280ft = Large Wooden Reel
Flexibility	Continuous flexing		
Voltage Rating	600V rated (UL)		
Conductors	7 conductors (includes ground)		
Conductor Size	16 AWG (1.50mm ²)		
Conductor Stranding	82-stranded		
Conductor Material	Bare copper		
Conductor Insulation Material	TPE		

Agency Approvals

UL Listed File #	E197090
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes with Exemptions (See CE Doc)
EU REACH	View EU REACH document