

# BTF1M-TDTL-P Cut Sheet



Autonics photoelectric sensor, rectangular, polybutylene terephthalate housing, through-beam pair, visible red, 0-1m sensing distance, 10.8-26.4 VDC operating voltage, light-on, PNP, 3-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BTF1M-TDTL-P>

## Technical Specifications

Brand	Autonics
Item	Photoelectric sensor
Shape	Rectangular
Housing Size	15.8 x 13 x 3.7mm
IP Rating	IP67
Application	Small space and standard duty
Housing Material	Polybutylene terephthalate
Sensing Method	Through-beam pair
Operating Voltage	10.8-26.4 VDC
Number of Wires	3
Switching Output	PNP

Sensing Distance	0-1m
Operation Mode	Light-on
Switching Frequency	1 kHz
Light Emission (NP)	Visible red
IO-Link Compatible	No
Cable Length	6.5ft/2m
Jacket Material	PVC
Connection	Pigtail
Conductor Size	28 AWG
Includes	Mounting hardware

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/BTF1M-TDTL-P.pdf>  
See store item page for other formats.