

A60-8M20-SPBO-22M Cut Sheet



Sung-II Machinery timing pulley, aluminum, 8mm 8M pitch, 60 tooth, 6.015in pitch diameter, 22mm bore, no hub with flanges. For use with 20mm wide belt. QD bushing included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A60-8M20-SPBO-22M>

Technical Specifications

Brand	Sung-II Machinery
Item	Timing pulley
Material	Aluminum
Pitch	8mm 8M
Number of Teeth	60
Pitch Diameter	6.015in
Bore Diameter	22mm
Pulley Type	No hub with flanges
Mounting Type	QD style bushing
For Use With	20mm wide belt
Includes	QD bushing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
[https://cdn.automationdirect.com/
/static/drawings/2d/A60-8M20-SPBO-22M.pdf](https://cdn.automationdirect.com/static/drawings/2d/A60-8M20-SPBO-22M.pdf)
See store item page for other formats.