

BX-DM1-10ER-D Cut Sheet



BRX Do-more PLC, 12-24 VDC required, serial port, microSD card slot, Discrete Input: 6-point, AC/DC, Discrete Output: 4-point, relay.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-DM1-10ER-D>

Technical Specifications

Brand	BRX Do-more	Nominal Output Voltage	12-48 VDC/24-240 VAC
Item	PLC	Discrete Output Type	Relay
Total Memory	192k words	Relay Configuration	(4) Form A (SPST) relays
Ladder Memory	64k words	Load Current	2A/point
User Data Memory	128k words	Number of Isolated Discrete Output Commons	2
Removable Media Type	MicroSD card slot	Number of Points per Discrete Output Common	2
Programming Language	Ladder	Maximum Number of PID Loops	100+ (configurable to memory limit)
Programming Software	Do-more Designer programming software v2.0 or later	Number of High-Speed Capable Input Points	6
Communication Port and Connection Type(s)	(1) RS-232/RS-485 (3-pin terminal)	High-Speed Counter(s)	<ul style="list-style-type: none">• up to (3) up counters• up to (3) down counters• up to (3) up/down counters• up to (3) pulse/direction (bi-directional) counters• up to (3) quadrature (A and B) counters• up to (3) quadrature (A and B with Z) counters
Port Protocol(s)	<ul style="list-style-type: none">• Do-more protocol• Modbus RTU Master/Slave• ASCII In/out• K-sequence Slave• webserver (non-secure HTTP)• programming and monitoring	Position Scaling	<ul style="list-style-type: none">• up to (3) up counters• up to (3) down counters• up to (3) up/down counters• up to (3) pulse/direction (bi-directional) counters• up to (3) quadrature (A and B) counters• up to (3) quadrature (A and B with Z) counters
Port Speed(s)	up to 115.2k baud	Interval Measurement	<ul style="list-style-type: none">• up to (3) single input (edge) timers• up to (3) dual input (dual edge) timers
Real Time Clock/Calendar	Yes	Duration Measurement	up to (3) single input (edge) timers
Retentive Memory	Yes	Frequency Measurement	<ul style="list-style-type: none">• up to (3) single input up counters• up to (3) single input down counters• up to (3) pulse/direction (bi-directional) counters• up to (3) quadrature input (A and B) counters• up to (3) quadrature (A and B with Z) counters• up to (3) edge timers interval scaling• up to (3) dual edge timers interval scaling
Battery Backup	Yes	Interrupt(s)	<ul style="list-style-type: none">• up to (4) input interrupts• up to (4) timer interrupts• up to (4) match register interrupts
Maximum Expansion Modules Allowed	2	Includes	BX-RTB03S terminal block and D0-MC-BAT battery
External Power Requirement	12-24 VDC		
Number of Discrete Input Points	6		
Nominal Input Voltage	12-24 VAC/VDC		
Voltage Type	AC/DC		
Discrete Input Type	Sinking/sourcing		
Number of Isolated Discrete Input Commons	2		
Number of Points per Discrete Input Common	3		
Frequency Response	250 kHz		
Number of Discrete Output Points	4		

BX-DM1-10ER-D Cut Sheet

Requires	BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Batteries• Battery Type: Button• Lithium Content: 0.07• Replacement Battery: D0-MC-BAT• Generic Battery: CR2032

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BX-DM1-10ER-D.pdf>
See store item page for other formats.