

BX-DM1-18AR Cut Sheet



BRX Do-more PLC, 120-240 VAC required, serial port, microSD card slot, Discrete Input: 10-point, AC, Discrete Output: 8-point, relay.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-DM1-18AR>

Technical Specifications

Brand	BRX Do-more
Item	PLC
Total Memory	192k words
Ladder Memory	64k words
User Data Memory	128k words
Removable Media Type	MicroSD card slot
Programming Language	Ladder
Programming Software	Do-more Designer programming software v2.0 or later
Communication Port and Connection Type(s)	(1) RS-232/RS-485 (3-pin terminal)
Port Protocol(s)	<ul style="list-style-type: none">• Do-more protocol• Modbus RTU Master/Slave• ASCII In/out• K-sequence Slave• webserver (non-secure HTTP)• programming and monitoring
Port Speed(s)	up to 115.2k baud
Real Time Clock/Calendar	Yes
Retentive Memory	Yes
Battery Backup	Yes
Maximum Expansion Modules Allowed	4
External Power Requirement	120-240 VAC
Number of Discrete Input Points	10
Nominal Input Voltage	120-240 VAC
Voltage Type	AC
Number of Isolated Discrete Input Commons	2
Number of Points per Discrete Input Common	5
Number of Discrete Output Points	8
Nominal Output Voltage	12-48 VDC/24-240 VAC
Discrete Output Type	Relay

Relay Configuration	(8) Form A (SPST) relays
Load Current	2A/point
Number of Isolated Discrete Output Commons	2
Number of Points per Discrete Output Common	4
Maximum Number of PID Loops	100+ (configurable to memory limit)
Includes	BX-RTB03S terminal block and D0-MC-BAT battery
Requires	BX-RTB18 or BX-RTB18-1 terminal block kit or ZIPLink pre-wired cables
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Batteries• Battery Type: Button• Lithium Content: 0.07• Replacement Battery: D0-MC-BAT• Generic Battery: CR2032

BX-DM1-18AR Cut Sheet

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
[https://cdn.automationdirect.com
/static/drawings/BX-DM1-18AR.pdf](https://cdn.automationdirect.com/static/drawings/BX-DM1-18AR.pdf)
See store item page for other formats.
