

BX-DM1E-10ER3-D Cut Sheet



BRX Do-more PLC, 12-24 VDC required, Ethernet and serial ports, microSD card slot, Discrete Input: 6-point, AC/DC, Analog Input: 1-channel, current/voltage, Discrete Output: 4-point, relay, Analog Output: 1-channel, current/voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-DM1E-10ER3-D>

Technical Specifications

Brand	BRX Do-more	Number of Points per Discrete Input Common	3
Item	PLC	Frequency Response	250 kHz
Total Memory	192k words	Number of Discrete Output Points	4
Ladder Memory	64k words	Nominal Output Voltage	12-48 VDC/24-240 VAC
User Data Memory	128k words	Discrete Output Type	Relay
Removable Media Type	MicroSD card slot	Relay Configuration	(4) Form A (SPST) relays
Programming Language	Ladder	Load Current	2A/point
Programming Software	Do-more Designer programming software v2.0 or later	Number of Isolated Discrete Output Commons	2
Communication Port and Connection Type(s)	<ul style="list-style-type: none">(1) Ethernet 10/100Base-T (RJ45)(1) RS-232/RS-485 (3-pin terminal)	Number of Points per Discrete Output Common	2
Port Protocol(s)	<ul style="list-style-type: none">Do-more protocolMQTT ClientFTP ClientModbus RTU Master/SlaveModbus TCPTCP/IPEtherNet/IP explicit messaging scanner/adaptorEthernet remote I/OK-sequence Slaveprogramming and monitoring	Number of Analog Input Channels	1
Port Speed(s)	<ul style="list-style-type: none">10/100 Mbpsup to 115.2k baud	Analog Input Signal Type	Current/voltage
Real Time Clock/Calendar	Yes	Number of Non-Isolated Analog Input Commons	1
Retentive Memory	Yes	Number of Points per Analog Input Common	1
Battery Backup	Yes	Input Resolution	16-bit
Maximum Expansion Modules Allowed	2	Input Current Signal Range	4-20 mA, +/- 20 mA
External Power Requirement	12-24 VDC	Input Voltage Signal Range	0-5 VDC, 0-10 VDC, +/- 5 VDC, +/- 10 VDC
Number of Discrete Input Points	6	Number of Analog Output Channels	1
Nominal Input Voltage	12-24 VAC/VDC	Analog Output Signal Type	Current/voltage
Voltage Type	AC/DC	Number of Non-Isolated Analog Output Commons	1
Discrete Input Type	Sinking/sourcing	Number of Points per Analog Output Common	1
Number of Isolated Discrete Input Commons	2	Output Resolution	16-bit
		Output Current Signal Range	4-20 mA and +/- 20 mA
		Output Voltage Signal Range	0-5 VDC, 0-10 VDC, +/- 5 VDC and +/- 10 VDC

BX-DM1E-10ER3-D Cut Sheet

Maximum Number of PID Loops	100+ (configurable to memory limit)	Interrupt(s)	<ul style="list-style-type: none">• up to (4) input interrupts• up to (4) timer interrupts• up to (4) match register interrupts
Number of High-Speed Capable Input Points	6	Includes	BX-RTB03S terminal block and D0-MC-BAT battery
High-Speed Counter(s)	<ul style="list-style-type: none">• up to (3) up counters• up to (3) down counters• up to (3) up/down counters• up to (3) pulse/direction (bi-directional) counters• up to (3) quadrature (A and B) counters• up to (3) quadrature (A and B with Z) counters	Requires	BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables
Position Scaling	<ul style="list-style-type: none">• up to (3) up counters• up to (3) down counters• up to (3) up/down counters• up to (3) pulse/direction (bi-directional) counters• up to (3) quadrature (A and B) counters• up to (3) quadrature (A and B with Z) counters		
Interval Measurement	<ul style="list-style-type: none">• up to (3) single input (edge) timers• up to (3) dual input (dual edge) timers		
Duration Measurement	up to (3) single input (edge) timers		
Frequency Measurement	<ul style="list-style-type: none">• up to (3) single input up counters• up to (3) single input down counters• up to (3) pulse/direction (bi-directional) counters• up to (3) quadrature input (A and B) counters• up to (3) quadrature (A and B with Z) counters• up to (3) edge timers interval scaling• up to (3) dual edge timers interval scaling		

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document