

BX-DM1E-36AR3 Cut Sheet



BRX Do-more PLC, 120-240 VAC required, Ethernet and serial ports, microSD card slot, Discrete Input: 20-point, AC, Analog Input: 4-channel, current/voltage, Discrete Output: 16-point, relay, Analog Output: 2-channel, current/voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-DM1E-36AR3>

Technical Specifications

Brand	BRX Do-more
Item	PLC
Total Memory	192k words
Ladder Memory	64k words
User Data Memory	128k words
Removable Media Type	MicroSD card slot
Programming Language	Ladder
Programming Software	Do-more Designer programming software v2.0 or later
Communication Port and Connection Type(s)	<ul style="list-style-type: none"> • (1) Ethernet 10/100Base-T (RJ45) • (1) RS-232/RS-485 (3-pin terminal)
Port Protocol(s)	<ul style="list-style-type: none"> • MQTT Client • MQTTs Client • FTP Client • Do-more protocol • Modbus RTU Master/Slave • Modbus TCP • TCP/IP • EtherNet/IP explicit messaging scanner/adaptor • EtherNet/IP implicit messaging scanner/adaptor • Ethernet remote I/O • K-sequence Slave • webservice (non-secure HTTP) • programming and monitoring
Port Speed(s)	<ul style="list-style-type: none"> • 10/100 Mbps • up to 115.2k baud
Real Time Clock/Calendar	Yes
Retentive Memory	Yes
Battery Backup	Yes
Maximum Expansion Modules Allowed	8
External Power Requirement	120-240 VAC
Number of Discrete Input Points	20
Nominal Input Voltage	120-240 VAC
Voltage Type	AC
Number of Isolated Discrete Input Commons	5

Number of Points per Discrete Input Common	4
Number of Discrete Output Points	16
Nominal Output Voltage	12-48 VDC/24-240 VAC
Discrete Output Type	Relay
Relay Configuration	(16) Form A (SPST) relays
Load Current	2A/point
Number of Isolated Discrete Output Commons	4
Number of Points per Discrete Output Common	4
Number of Analog Input Channels	4
Analog Input Signal Type	Current/voltage
Number of Non-Isolated Analog Input Commons	1
Number of Points per Analog Input Common	4
Input Resolution	16-bit
Input Current Signal Range	Input current signal range(s) of 4-20 mA, +/- 20 mA
Input Voltage Signal Range	Input voltage signal range(s) of 0-5 VDC, 0-10 VDC, +/- 5 VDC, +/- 10 VDC
Number of Analog Output Channels	2
Analog Output Signal Type	Current/voltage
Number of Non-Isolated Analog Output Commons	3
Number of Points per Analog Output Common	2
Output Resolution	16-bit
Output Current Signal Range	4-20 mA and +/- 20 mA
Output Voltage Signal Range	0-5 VDC, 0-10 VDC, +/- 5 VDC and +/- 10 VDC
Maximum Number of PID Loops	100+ (configurable to memory limit)

BX-DM1E-36AR3 Cut Sheet

Includes	BX-RTB03S terminal block and D0-MC-BAT battery
Requires	BX-RTB36 or BX-RTB36-1 terminal block kit or ZIPLink pre-wired cables
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Batteries• Battery Type: Button• Lithium Content: 0.07• Replacement Battery: D0-MC-BAT• Generic Battery: CR2032

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BX-DM1E-36AR3.pdf>
See store item page for other formats.