


C0-02DD1-D Cut Sheet



CLICK Analog PLC, 24 VDC required, serial ports, Discrete Input: 4-point, DC, Analog Input: 2-channel, current/voltage, Discrete Output: 4-point, sinking, Analog Output: 2-channel, current/voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-02DD1-D>

Technical Specifications

Brand	CLICK
Item	PLC
Series	Analog
Ladder Memory	8k steps
User Data Memory	16 KB
Programming Language	Ladder
Programming Software	CLICK programming software v1.12 or later and CLICK CPU firmware v1.10 or later
Communication Port and Connection Type(s)	<ul style="list-style-type: none"> • (2) RS-232 (RJ12) • (1) RS-485 (3-pin terminal)
Port Protocol(s)	<ul style="list-style-type: none"> • Modbus RTU Master/Slave • ASCII In/out • programming and monitoring
Port Speed(s)	up to 115.2k baud
Real Time Clock/Calendar	Yes
Retentive Memory	Yes
Battery Backup	Yes
Maximum Expansion Modules Allowed	8
External Power Requirement	24 VDC
Number of Discrete Input Points	4
Nominal Input Voltage	24 VDC
Voltage Type	DC
Discrete Input Type	Sinking/sourcing
Number of Isolated Discrete Input Commons	1
Number of Points per Discrete Input Common	4
Number of Discrete Output Points	4
Nominal Output Voltage	5-27 VDC
Discrete Output Type	Sinking
Load Current	0.1A/point

Number of Isolated Discrete Output Commons	1
Number of Points per Discrete Output Common	4
Number of Analog Input Channels	2
Analog Input Signal Type	Current/voltage
Number of Non-Isolated Analog Input Commons	1
Number of Points per Analog Input Common	2
Input Resolution	12-bit
Input Current Signal Range	4-20 mA
Input Voltage Signal Range	0-5 VDC
Number of Analog Output Channels	2
Analog Output Signal Type	Current/voltage
Number of Non-Isolated Analog Output Commons	1
Number of Points per Analog Output Common	2
Output Resolution	12-bit
Output Current Signal Range	4-20 mA
Output Voltage Signal Range	0-5 VDC
Includes	Removable terminal block
Additional Information	Purchase D2-BAT-1 backup battery separately

C0-02DD1-D Cut Sheet

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/C0-02DD1-D.pdf>
See store item page for other formats.
