

# C167A Cut Sheet



Marathon standard efficiency AC induction motor, general purpose, 1/2hp, 1-phase, 115/230 VAC, suitable for 208 VAC at 60 Hz, 1800rpm, ODP, 56 frame, rolled steel, rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C167A>

## Technical Specifications

<b>Brand</b>	Marathon
<b>Item</b>	Motor
<b>Efficiency Group</b>	Standard efficiency
<b>Efficiency</b>	76.2
<b>Voltage Type</b>	AC
<b>Motor Type</b>	Induction
<b>Motor Application</b>	General purpose
<b>Horsepower Rating</b>	1/2hp
<b>Number of Phases</b>	1
<b>Voltage Rating</b>	115/230 VAC, suitable for 208 VAC at 60 Hz
<b>Synchronous Speed</b>	1800rpm
<b>Nameplate RPM</b>	1725rpm
<b>Overload Type</b>	None
<b>Enclosure Type</b>	ODP
<b>Shaft Type</b>	Round with square key

<b>Shaft Diameter</b>	5/8in
<b>Shaft Material</b>	1144 Stressproof (C-223) steel
<b>Motor Frame</b>	56
<b>Frame Material</b>	Rolled steel
<b>Electrically Reversible</b>	Yes
<b>Insulation Class</b>	Class B
<b>IP Rating</b>	IP22
<b>Service Factor</b>	1.25
<b>Integrated Brake</b>	No
<b>NEMA Design</b>	Design N
<b>Junction Box Orientation</b>	F1
<b>Mounting</b>	Rigid base
<b>Mounting Orientation</b>	Horizontal
<b>Manufacturer Part Number</b>	056B17D11018

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E49747
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR2025
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>