


C2-14D1 Cut Sheet



CLICK PLUS discrete combo module, Input: 8-point, 24 VDC, sinking/sourcing, Output: 6-point, 5-27 VDC, sinking, 0.1A/point. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C2-14D1>

Technical Specifications

Brand	CLICK PLUS
Item	Combo module
I/O Module Type	Discrete
Number of Input Points	8
Nominal Input Voltage	24 VDC
Discrete Input Type	Sinking/sourcing
Number of Isolated Discrete Input Commons	2
Number of Points per Discrete Input Common	4
Number of Output Points	6
Nominal Output Voltage	5-27 VDC
Discrete Output Type	Sinking
Number of Isolated Discrete Output Commons	2
Number of Points per Discrete Output Common	4/2
Load Current	0.1A/point
Fuse Type	User-supplied external fuse
Number of High-Speed Capable Input Points	8
High-Speed Counter(s)	<ul style="list-style-type: none">• up to (6) up counters• up to (6) down counters• up to (3) up/down counters• up to (4) pulse/direction (bi-directional) counters• up to (4) quadrature (A and B) counters• up to (2) quadrature (A and B with Z) counters
Interval Measurement	<ul style="list-style-type: none">• up to (6) single input (edge) timers• up to (3) dual input (dual edge) timers
Duration Measurement	up to (6) single input (edge) timers
Frequency Measurement	<ul style="list-style-type: none">• up to (6) single input up counters• up to (4) quadrature input (A and B) counters
Interrupt(s)	<ul style="list-style-type: none">• up to (8) input interrupts• up to (4) timer interrupts
Table-Driven Input(s)	up to (6) preset tables
Maximum Switching Frequency	100 kHz

Number of High-Speed Capable Output Points	3
Number of Output Channels	3
Pulse Output Channel Type	NPN open collector
Output Pulse Mode(s)	<ul style="list-style-type: none">• up to (3) virtual axes• up to (3) PTO linear step/direction outputs• up to (3) PWM pulse width modulation outputs
Axis Profile(s)	<ul style="list-style-type: none">• relative/absolute positioning• multi-axis interpolation• velocity mode• trapezoid• S-curve• registration• homing• jogging• linear mode
Includes	Removable terminal block
Programming Software	CLICK programming software v3.3 or later and CLICK CPU firmware v3.3 or later

C2-14D1 Cut Sheet

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/C2-14D1.pdf>
See store item page for other formats.