

# CR8-AN-1F Cut Sheet



AutomationDirect inductive proximity sensor, rectangular, 8 x 8 x 59mm body, nickel-plated brass housing, NPN, N.O. output, 1.5mm sensing distance, flush, 1 kHz switching frequency, IP67, 3-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CR8-AN-1F>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Proximity sensor
<b>Sensor Type</b>	Inductive
<b>Application</b>	Standard duty and small space
<b>Shape</b>	Rectangular
<b>Housing Size</b>	8 x 8 x 59mm body
<b>Housing Material</b>	Nickel-plated brass
<b>Sensing Method</b>	Standard sensing
<b>Adjustable</b>	No
<b>Number of Wires</b>	3
<b>Switching Output</b>	NPN
<b>Operation Mode</b>	N.O. output
<b>Sensing Distance</b>	1.5mm
<b>Mounting Type</b>	Flush
<b>IO-Link Compatible</b>	No
<b>Switching Frequency</b>	1 kHz
<b>Operating Voltage</b>	10-30 VDC
<b>Operating Temperature</b>	-25 to 70c
<b>Weld Field Immune</b>	No
<b>Chip Immune</b>	No
<b>IP Rating</b>	IP67
<b>Connection</b>	3-pin M8 quick-disconnect
<b>Includes</b>	Mounting hardware
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E328811
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>