


CSM105WA Cut Sheet



Metrol limit switch, precision touch, 10mm diameter, threaded, 0.5mm pitch, 15mm length, 2.5mm radius head, stainless steel, 3.5mm plunger, 1N contact force, N.O. contact(s), 1.6ft/0.5m cable length, core wire.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CSM105WA>

Technical Specifications

Brand	Metrol
Item	Limit switch
Switch Type	Precision touch
Diameter	10mm
Barrel Type	Threaded
Length	15mm
Head Type	2.5mm radius
Actuator Type	3.5mm plunger
Contact Force	1N
Contact Type	N.O.
Cable Length	1.6ft/0.5m
Connection	Core wire
Conductor Size	32 AWG
Stroke	1.5mm
Repeatability	0.003mm
Thread Pitch	0.5mm
Material	Stainless steel
IP Rating	IP65
Operating Temperature	0 to 80 deg C
Includes	Mounting hardware

Agency Approvals

RoHS Status	No
EU REACH	View EU REACH document