

APM-FE16DMK-AD Cut Sheet



LS Electric medium inertia AC brushless servo motor, 1.6 kW, 3-phase input, 19-bit (524288 ppr) encoder. For use with LS Electric L7PA020U-AD and iX7NHA020U-AD with 3-phase input and L7PA035U-AD and iX7NHA035U-AD with 1-phase input.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/APM-FE16DMK-AD>

Technical Specifications

Brand	LS Electric
Item	Servo motor
Performance Level	Medium inertia
Voltage Type	AC
Motor Type	Brushless
Power Rating	1.6 kW
Number of Input Phases	3
Rated Speed	2000rpm
Maximum Speed	3000rpm
Amperage Rating	10.98A
Holding Torque Rating	67.5 lb-in
Encoder Resolution	19-bit (524288 ppr)
Integrated Brake	No

Motor Frame	130mm
IP Rating	IP65
Shaft Type	Single
Shaft Diameter	22mm
Steps per Revolution	Up to 19-bit (524288 ppr)
For Use With	LS Electric L7PA020U-AD and iX7NHA020U-AD with 3-phase input and L7PA035U-AD and iX7NHA035U-AD with 1-phase input
Includes	Motor shaft key
Requires	LS Electric APCS-PxxxxHS-AD power cables and APCS-ExxxxDS1-AD encoder cables
Additional Information	For 1-phase supply: Use L7PA035U-AD 3.5 kW drive

Agency Approvals

UL Listed File #	E255738
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/APM-FE16DMK-AD.pdf>
See store item page for other formats.