

APM-FEP22DMK-AD Cut Sheet



LS Electric medium inertia AC brushless servo motor, 2.2 kW, 3-phase input, 19-bit (524288 ppr) encoder. For use with LS Electric L7PB020U-AD 2 kW drive.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/APM-FEP22DMK-AD>

Technical Specifications

| | |
|-------------------------------|--|
| Brand | LS Electric |
| Item | Servo motor |
| Performance Level | Medium inertia |
| Voltage Type | AC |
| Motor Type | Brushless |
| Power Rating | 2.2 kW |
| Number of Input Phases | 3 |
| Rated Speed | 2000rpm |
| Maximum Speed | 3000rpm |
| Amperage Rating | 6.8A |
| Holding Torque Rating | 92.9 lb-in |
| Encoder Resolution | 19-bit (524288 ppr) |
| Integrated Brake | No |
| Motor Frame | 130mm |
| IP Rating | IP65 |
| Shaft Type | Single |
| Shaft Diameter | 24mm |
| Steps per Revolution | Up to 19-bit (524288 ppr) |
| For Use With | LS Electric L7PB020U-AD 2 kW drive |
| Includes | Motor shaft key |
| Requires | LS Electric APCS-PxxxxHS-AD power cables and APCS-ExxxxDS1-AD encoder cables |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E255738 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |