

# D0-06DR-D Cut Sheet



DirectLOGIC DL06 PLC, 12-24 VDC required, serial ports, Discrete Input: 20-point, DC, Discrete Output: 16-point, relay.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D0-06DR-D>

## Technical Specifications

<b>Brand</b>	DirectLOGIC
<b>Item</b>	PLC
<b>Series</b>	DL06
<b>Total Memory</b>	14.8k words
<b>Ladder Memory</b>	7k words
<b>User Data Memory</b>	7k words
<b>Programming Language</b>	Ladder
<b>Programming Software</b>	DirectSOFT programming software v4.0 or later
<b>Communication Port and Connection Type(s)</b>	<ul style="list-style-type: none"> <li>• (1) RS-232 (RJ12)</li> <li>• (1) RS-232/RS-422/RS-485 (DB15HD female)</li> </ul>
<b>Port Protocol(s)</b>	<ul style="list-style-type: none"> <li>• DirectNET</li> <li>• Modbus RTU</li> <li>• ASCII</li> <li>• K-sequence</li> <li>• programming and monitoring</li> </ul>
<b>Port Speed(s)</b>	<ul style="list-style-type: none"> <li>• fixed at 9.6k baud</li> <li>• up to 38.4k baud</li> </ul>
<b>Real Time Clock/Calendar</b>	Yes
<b>Retentive Memory</b>	Yes
<b>Battery Backup</b>	Yes
<b>Maximum Expansion Modules Allowed</b>	4
<b>External Power Requirement</b>	12-24 VDC
<b>Number of Discrete Input Points</b>	20
<b>Nominal Input Voltage</b>	12-24 VDC
<b>Voltage Type</b>	DC
<b>Discrete Input Type</b>	Sinking/sourcing
<b>Number of Isolated Discrete Input Commons</b>	5
<b>Number of Points per Discrete Input Common</b>	4
<b>Frequency Response</b>	7 kHz
<b>Number of Discrete Output Points</b>	16

<b>Nominal Output Voltage</b>	6-24 VDC/6-240 VAC
<b>Discrete Output Type</b>	Relay
<b>Relay Configuration</b>	(16) Form A (SPST) relays
<b>Load Current</b>	2A/point
<b>Number of Isolated Discrete Output Commons</b>	4
<b>Number of Points per Discrete Output Common</b>	4
<b>Maximum Number of PID Loops</b>	8
<b>Number of High-Speed Capable Input Points</b>	4
<b>High-Speed Counter(s)</b>	<ul style="list-style-type: none"> <li>• up to (2) up counters</li> <li>• up to (1) down counter</li> <li>• up to (1) up/down counter</li> <li>• up to (1) quadrature (A and B) counter</li> </ul>
<b>Position Scaling</b>	<ul style="list-style-type: none"> <li>• up to (2) up counters</li> <li>• up to (1) down counter</li> <li>• up to (1) up/down counter</li> <li>• up to (1) quadrature (A and B) counter</li> </ul>
<b>Frequency Measurement</b>	<ul style="list-style-type: none"> <li>• up to (2) up counters</li> <li>• up to (1) down counter</li> <li>• up to (1) up/down counter</li> <li>• up to (1) quadrature (A and B) counter</li> </ul>
<b>Interrupt(s)</b>	<ul style="list-style-type: none"> <li>• up to (1) input interrupt</li> <li>• up to (1) timer interrupt</li> </ul>
<b>Additional Information</b>	Purchase D2-BAT-1 backup battery separately

# D0-06DR-D Cut Sheet

---

## Agency Approvals

<b>UL Listed File #</b>	E157382
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	E200031
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

---

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/D0-06DR-D.pdf>  
See store item page for other formats.

---