

# DEFINE-REPEATER Cut Sheet



Define Instruments Twin Link series wireless signal repeater, ZigBee: 2.4 GHz, 9-36 VDC operating voltage, 35mm DIN rail mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DEFINE-REPEATER>

## Technical Specifications

<b>Brand</b>	Define Instruments
<b>Item</b>	Wireless signal repeater
<b>Series</b>	Twin Link
<b>Field Configurable</b>	Yes
<b>Communication Port and Connection Type(s)</b>	(1) ZigBee (RP-SMA antenna plug)
<b>Port Speed(s)</b>	802.15.4 ZigBee
<b>Frequency Bands</b>	ZigBee: 2.4 GHz
<b>Operating Voltage</b>	9-36 VDC

<b>Housing Material</b>	Plastic
<b>IP Rating</b>	IP20
<b>Mounting</b>	35mm DIN rail
<b>Electrical Connection</b>	Screw terminals
<b>Requires</b>	DEFINE-BRIDGE-KEY fob USB adapter and DEFINE-TOOLBOX-SW configuration software
<b>Additional Information</b>	Use STRIDE SE-ANT250 dome antenna for installation in metal enclosures

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/DEFINE-REPEATER.pdf>  
See store item page for other formats.