

DGA-10 Cut Sheet



ProSense differential pressure gauge, 4in dial diameter, 0 to 10.0in of water column, black die-cast aluminum case, aluminum and silicone rubber wetted parts, (2) high and (2) low 1/8in female NPT process connection, panel or surface mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DGA-10>

Technical Specifications

Brand	ProSense
Item	Differential pressure gauge
Diameter	4in dial
Scale	0 to 10.0in of water column
Case Type	Black die-cast aluminum
Wetted Parts	Aluminum and silicone rubber
Process Connection	(2) high and (2) low 1/8in female NPT
Mounting	Panel or surface

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DGA-10.pdf>
See store item page for other formats.