

# ASD-22-120A Cut Sheet



NITRA soft start valve, 3-port (3-way), 2-position, single solenoid spring return, N.C., 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 1/4in female NPT exhaust(s), Cv=7.5, 120 VAC operating voltage. For use with Ax-22 series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ASD-22-120A>

## Technical Specifications

|                       |                                  |
|-----------------------|----------------------------------|
| Brand                 | NITRA                            |
| Item                  | Valve                            |
| Working Fluid         | Air                              |
| Valve Type            | Soft start                       |
| Action                | Single solenoid spring return    |
| Port Quantity         | 3-port (3-way)                   |
| Number Of Positions   | 2                                |
| Valve Configuration   | N.C.                             |
| Inlet Port            | 1/4in female NPT                 |
| Outlet Port           | 1/4in female NPT                 |
| Exhaust Port          | 1/4in female NPT                 |
| Flow Coefficient      | 7.5                              |
| Operating Voltage     | 120 VAC                          |
| Electrical Connection | DIN style wiring connector       |
| Indicating Type       | LED indication                   |
| For Use With          | Ax-22 series air prep components |
| Includes              | T-bracket                        |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |