


DM860E Cut Sheet



Leadshine DC microstepping stepper drive, 7.2A per phase, 2-phase output, 24-70 VDC, bipolar, position mode, 400 to 51200 steps per revolution.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DM860E>

Technical Specifications

Brand	Leadshine
Item	Stepper drive
Controller Type	Microstepping
Voltage Type	DC
Amperage Rating	7.2A per phase
Number of Output Phases	2
Nominal Input Voltage	24-70 VDC
Winding Type Control	Bipolar
Output Type	MOSFET, dual H-bridge and 4-quadrant output
Steps per Revolution	400 to 51200
Temperature Rating	0 to 65 deg C
Enclosure Type	Enclosed
IP Rating	IP20
Mounting	Panel

Control Mode	Position
Command Signal(s)	<ul style="list-style-type: none">• step and direction• CW/CCW
Number of Discrete Input Points	1
Discrete Input Type	Sinking/sourcing/line driver (differential)
Tuning Mode	Pre-tuned
Idle Current Reduction	Yes
Drive Features	Anti-resonance (electronic damping) and auto motor matching (self-configuration)
Protection Type(s)	<ul style="list-style-type: none">• overvoltage• overcurrent
Configuration	Rotary dial, dipswitches or jumpers

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS 3 Document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DM860E.pdf>
See store item page for other formats.