

# AT1-AN-4A Cut Sheet



Micro Detectors inductive proximity sensor, tubular, 30mm diameter x 60mm body, nickel-plated brass housing, NPN, N.O. output, 20mm sensing distance, non-flush, 150 Hz switching frequency, IP67, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AT1-AN-4A>

## Technical Specifications

<b>Brand</b>	Micro Detectors	<b>Sensing Distance</b>	20mm
<b>Item</b>	Proximity sensor	<b>Mounting Type</b>	Non-flush
<b>Sensor Type</b>	Inductive	<b>IO-Link Compatible</b>	No
<b>Application</b>	Standard duty	<b>Switching Frequency</b>	150 Hz
<b>Shape</b>	Tubular	<b>Operating Voltage</b>	10-30 VDC
<b>Housing Size</b>	30mm diameter x 60mm body	<b>Operating Temperature</b>	-25 to 70c
<b>Housing Material</b>	Nickel-plated brass	<b>Weld Field Immune</b>	No
<b>Barrel Type</b>	Threaded	<b>Chip Immune</b>	No
<b>Sensing Method</b>	Extended sensing	<b>IP Rating</b>	IP67
<b>Adjustable</b>	No	<b>Connection</b>	Pigtail
<b>Number of Wires</b>	3	<b>Conductor Size</b>	21 AWG
<b>Switching Output</b>	NPN	<b>Cable Length</b>	6.5ft/2m
<b>Operation Mode</b>	N.O. output	<b>Includes</b>	Mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	Not Applicable
<b>UL Recognized File #</b>	E130644
<b>UL Hazardous File #</b>	Not Applicable
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>