

DPB-20-OPN Cut Sheet



PBC DPB series double roller pillow block, cam follower bearing, 3.37in overall length, steel, 1-1/4in inside diameter, aluminum housing, adjustable running clearance. For use with 1-1/4in diameter PBC shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPB-20-OPN>

Technical Specifications

Brand	PBC
Item	Double roller pillow block
Series	DPB
Block Type	Open type
Overall Length	3.37in
Bearing Type	Cam follower bearing
Bearing Material	Steel
Housing Fit	Fixed
Bearing Inside Diameter	1-1/4in
Housing Material	Aluminum
Running Clearance	Adjustable
For Use With	1-1/4in diameter PBC shafts

Agency Approvals

UL Listed File #	Not Applicable
UL Recognized File #	Not Applicable
UL Hazardous File #	Not Applicable
CE	None
CSA File #	Not Applicable
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DPB-20-OPN.pdf>
See store item page for other formats.