


BW9F0JA-15A Cut Sheet



Fuji Electric flange handle, lever, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 12. For use with Fuji Electric 630A and 800A frame MCCBs. 1.5m cable and MCCB terminal covers included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BW9F0JA-15A>

Technical Specifications

Brand	Fuji Electric
Item	Handle
Handle Type	Flange
Handle Style	Lever
Color	Black
Mounting	External front
Number Of Positions	2
Lockable Positions	ON-OFF
Defeatable	Yes
NEMA Rating	12
For Use With	Fuji Electric 630A and 800A frame MCCBs
Includes	1.5m cable and MCCB terminal covers

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document