

DW-AD-509-M18-320 Cut Sheet



Contrinex inductive proximity sensor, tubular, 18mm diameter x 36mm body, chrome-plated brass housing, 0-10 VDC or 4-20 mA analog output, 10mm sensing distance, semi-flush, IP67, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DW-AD-509-M18-320>

Technical Specifications

Brand	Contrinex
Item	Proximity sensor
Sensor Type	Inductive
Application	Standard duty and analog output
Shape	Tubular
Housing Size	18mm diameter x 36mm body
Housing Material	Chrome-plated brass
Barrel Type	Threaded
Sensing Method	Extended sensing
Adjustable	No
Number of Wires	4
Analog Output	0-10 VDC or 4-20 mA
Sensing Distance	10mm

Mounting Type	Semi-flush
IO-Link Compatible	No
Operating Voltage	15-30 VDC
Operating Temperature	-25 to 70c
Weld Field Immune	No
Chip Immune	No
IP Rating	IP67
Connection	Pigtail
Conductor Size	24 AWG
Cable Length	6.5ft/2m
Jacket Material	PUR
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E239373
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document