

# BX-DM1E-10AR3-D Cut Sheet



BRX Do-more PLC, 12-24 VDC required, Ethernet and serial ports, microSD card slot, Discrete Input: 6-point, AC, Analog Input: 1-channel, current/voltage, Discrete Output: 4-point, relay, Analog Output: 1-channel, current/voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-DM1E-10AR3-D>

## Technical Specifications

<b>Brand</b>	BRX Do-more	<b>Number of Points per Discrete Input Common</b>	3
<b>Item</b>	PLC	<b>Number of Discrete Output Points</b>	4
<b>Total Memory</b>	192k words	<b>Nominal Output Voltage</b>	12-48 VDC/24-240 VAC
<b>Ladder Memory</b>	64k words	<b>Discrete Output Type</b>	Relay
<b>User Data Memory</b>	128k words	<b>Relay Configuration</b>	(4) Form A (SPST) relays
<b>Removable Media Type</b>	MicroSD card slot	<b>Load Current</b>	2A/point
<b>Programming Language</b>	Ladder	<b>Number of Isolated Discrete Output Commons</b>	2
<b>Programming Software</b>	Do-more Designer programming software v2.0 or later	<b>Number of Points per Discrete Output Common</b>	2
<b>Communication Port and Connection Type(s)</b>	<ul style="list-style-type: none"> <li>(1) Ethernet 10/100Base-T (RJ45)</li> <li>(1) RS-232/RS-485 (3-pin terminal)</li> </ul>	<b>Number of Analog Input Channels</b>	1
<b>Port Protocol(s)</b>	<ul style="list-style-type: none"> <li>MQTT Client</li> <li>MQTTs Client</li> <li>FTP Client</li> <li>Do-more protocol</li> <li>Modbus RTU Master/Slave</li> <li>Modbus TCP</li> <li>TCP/IP</li> <li>EtherNet/IP explicit messaging scanner/adaptor</li> <li>EtherNet/IP implicit messaging scanner/adaptor</li> <li>Ethernet remote I/O</li> <li>K-sequence Slave</li> <li>programming and monitoring</li> </ul>	<b>Analog Input Signal Type</b>	Current/voltage
<b>Port Speed(s)</b>	<ul style="list-style-type: none"> <li>10/100 Mbps</li> <li>up to 115.2k baud</li> </ul>	<b>Number of Non-Isolated Analog Input Commons</b>	1
<b>Real Time Clock/Calendar</b>	Yes	<b>Number of Points per Analog Input Common</b>	1
<b>Retentive Memory</b>	Yes	<b>Input Resolution</b>	16-bit
<b>Battery Backup</b>	Yes	<b>Input Current Signal Range</b>	4-20 mA, +/- 20 mA
<b>Maximum Expansion Modules Allowed</b>	2	<b>Input Voltage Signal Range</b>	0-5 VDC, 0-10 VDC, +/- 5 VDC, +/- 10 VDC
<b>External Power Requirement</b>	12-24 VDC	<b>Number of Analog Output Channels</b>	1
<b>Number of Discrete Input Points</b>	6	<b>Analog Output Signal Type</b>	Current/voltage
<b>Nominal Input Voltage</b>	120-240 VAC	<b>Number of Non-Isolated Analog Output Commons</b>	1
<b>Voltage Type</b>	AC	<b>Number of Points per Analog Output Common</b>	1
<b>Number of Isolated Discrete Input Commons</b>	2	<b>Output Resolution</b>	16-bit
		<b>Output Current Signal Range</b>	4-20 mA and +/- 20 mA
		<b>Output Voltage Signal Range</b>	0-5 VDC, 0-10 VDC, +/- 5 VDC and +/- 10 VDC
		<b>Maximum Number of PID Loops</b>	100+ (configurable to memory limit)
		<b>Includes</b>	BX-RTB03S terminal block and D0-MC-BAT battery

# BX-DM1E-10AR3-D Cut Sheet

<b>Requires</b>	BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables
<b>Dangerous Goods</b>	<ul style="list-style-type: none"><li>• Battery Installed: Yes</li><li>• Packaging Instructions: 970</li><li>• UN Number: UN3091</li><li>• Hazard Type: Lithium Batteries</li><li>• Battery Type: Button</li><li>• Lithium Content: 0.07</li><li>• Replacement Battery: D0-MC-BAT</li><li>• Generic Battery: CR2032</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E185989
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BX-DM1E-10AR3-D.pdf>  
See store item page for other formats.