

BX-DM1E-18ER3 Cut Sheet



BRX Do-more PLC, 120-240 VAC required, Ethernet and serial ports, microSD card slot, Discrete Input: 10-point, AC/DC, Analog Input: 1-channel, current/voltage, Discrete Output: 8-point, relay, Analog Output: 1-channel, current/voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-DM1E-18ER3>

Technical Specifications

Brand	BRX Do-more
Item	PLC
Total Memory	192k words
Ladder Memory	64k words
User Data Memory	128k words
Removable Media Type	MicroSD card slot
Programming Language	Ladder
Programming Software	Do-more Designer programming software v2.0 or later
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (1) Ethernet 10/100Base-T (RJ45)• (1) RS-232/RS-485 (3-pin terminal)
Port Protocol(s)	<ul style="list-style-type: none">• MQTT Client• MQTTs Client• FTP Client• Do-more protocol• Modbus RTU Master/Slave• Modbus TCP• TCP/IP• EtherNet/IP explicit messaging scanner/adaptor• EtherNet/IP implicit messaging scanner/adaptor• Ethernet remote I/O• K-sequence Slave• webserver (non-secure HTTP)• programming and monitoring
Port Speed(s)	<ul style="list-style-type: none">• 10/100 Mbps• up to 115.2k baud
Real Time Clock/Calendar	Yes
Retentive Memory	Yes
Battery Backup	Yes
Maximum Expansion Modules Allowed	8
External Power Requirement	120-240 VAC
Number of Discrete Input Points	10
Nominal Input Voltage	12-24 VAC/VDC
Voltage Type	AC/DC
Discrete Input Type	Sinking/sourcing

Number of Isolated Discrete Input Commons	2
Number of Points per Discrete Input Common	5
Frequency Response	250 kHz
Number of Discrete Output Points	8
Nominal Output Voltage	12-48 VDC/24-240 VAC
Discrete Output Type	Relay
Relay Configuration	(8) Form A (SPST) relays
Load Current	2A/point
Number of Isolated Discrete Output Commons	2
Number of Points per Discrete Output Common	4
Number of Analog Input Channels	1
Analog Input Signal Type	Current/voltage
Number of Non-Isolated Analog Input Commons	1
Number of Points per Analog Input Common	1
Input Resolution	16-bit
Input Current Signal Range	Input current signal range(s) of 4-20 mA, +/- 20 mA
Input Voltage Signal Range	Input voltage signal range(s) of 0-5 VDC, 0-10 VDC, +/- 5 VDC, +/- 10 VDC
Number of Analog Output Channels	1
Analog Output Signal Type	Current/voltage
Number of Non-Isolated Analog Output Commons	1
Number of Points per Analog Output Common	1
Output Resolution	16-bit
Output Current Signal Range	4-20 mA and +/- 20 mA

BX-DM1E-18ER3 Cut Sheet

Output Voltage Signal Range	0-5 VDC, 0-10 VDC, +/- 5 VDC and +/- 10 VDC
Maximum Number of PID Loops	100+ (configurable to memory limit)
Number of High-Speed Capable Input Points	10
High-Speed Counter(s)	<ul style="list-style-type: none">• up to (3) up counters• up to (3) down counters• up to (3) up/down counters• up to (3) pulse/direction (bi-directional) counters• up to (3) quadrature (A and B) counters• up to (3) quadrature (A and B with Z) counters
Position Scaling	<ul style="list-style-type: none">• up to (3) up counters• up to (3) down counters• up to (3) up/down counters• up to (3) pulse/direction (bi-directional) counters• up to (3) quadrature (A and B) counters• up to (3) quadrature (A and B with Z) counters
Interval Measurement	<ul style="list-style-type: none">• up to (3) single input (edge) timers• up to (3) dual input (dual edge) timers
Duration Measurement	up to (3) single input (edge) timers
Frequency Measurement	<ul style="list-style-type: none">• up to (3) single input up counters• up to (3) single input down counters• up to (3) pulse/direction (bi-directional) counters• up to (3) quadrature input (A and B) counters• up to (3) quadrature (A and B with Z) counters• up to (3) edge timers interval scaling• up to (3) dual edge timers interval scaling
Interrupt(s)	<ul style="list-style-type: none">• up to (4) input interrupts• up to (4) timer interrupts• up to (4) match register interrupts
Includes	BX-RTB03S terminal block and D0-MC-BAT battery
Requires	BX-RTB18 or BX-RTB18-1 terminal block kit or ZIPLink pre-wired cables
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Batteries• Battery Type: Button• Lithium Content: 0.07• Replacement Battery: D0-MC-BAT• Generic Battery: CR2032

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BX-DM1E-18ER3.pdf>
See store item page for other formats.