

DW-AS-503-M30-002 Cut Sheet



Contrinex inductive proximity sensor, tubular, 30mm diameter x 73.5mm body, chrome-plated brass housing, PNP, N.O. output, 22mm sensing distance, semi-flush, 200 Hz switching frequency, IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DW-AS-503-M30-002>

Technical Specifications

| | |
|---------------------------|-----------------------------|
| Brand | Contrinex |
| Item | Proximity sensor |
| Sensor Type | Inductive |
| Application | Standard duty |
| Shape | Tubular |
| Housing Size | 30mm diameter x 73.5mm body |
| Housing Material | Chrome-plated brass |
| Barrel Type | Threaded |
| Sensing Method | Triple sensing |
| Adjustable | No |
| Number of Wires | 3 |
| Switching Output | PNP |
| Operation Mode | N.O. output |
| Sensing Distance | 22mm |
| Mounting Type | Semi-flush |
| IO-Link Compatible | Yes |

| | |
|--|---|
| Switching Frequency | 200 Hz |
| Operating Voltage | 10-30 VDC |
| Operating Temperature | -25 to 70c |
| Weld Field Immune | No |
| Chip Immune | No |
| IP Rating | IP67 |
| Connection | 4-pin M12 quick-disconnect |
| Communication Port and Connection Type(s) | (1) 4-pin M12 A-coded (IO-Link) port(s) |
| Port Protocol(s) | IO-Link Class A Device |
| Port Speed(s) | IO-Link COM2 |
| IO-Link Version | IO-Link v1.0 |
| Standard I/O Mode Supported | Yes |
| Includes | Mounting hardware |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E239373 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |