

DW-AS-503-P12-630 Cut Sheet



Contrinex inductive proximity sensor, tubular, 12mm diameter x 56mm body, 304 stainless steel housing, PNP, N.O., 1.5mm sensing distance, flush, 600 Hz switching frequency, IP68, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DW-AS-503-P12-630>

Technical Specifications

Brand	Contrinex
Item	Proximity sensor
Sensor Type	Inductive
Application	High pressure hydraulic
Shape	Tubular
Housing Size	12mm diameter x 56mm body
Housing Material	304 stainless steel
Barrel Type	Threaded
Sensing Method	Standard sensing
Adjustable	No
Number of Wires	3
Switching Output	PNP
Operation Mode	N.O.
Sensing Distance	1.5mm
Mounting Type	Flush
IO-Link Compatible	Yes
Switching Frequency	600 Hz

Operating Voltage	10-30 VDC
Operating Temperature	-25 to 100 deg C
Operating Pressure	7252psi (500 bar)
Weld Field Immune	No
Chip Immune	No
IP Rating	IP68
Connection	4-pin M12 quick-disconnect
Communication Port and Connection Type(s)	(1) 4-pin M12 A-coded (IO-Link) port(s)
Port Protocol(s)	IO-Link Class A Device
Port Speed(s)	IO-Link COM2
IO-Link Version	IO-Link v1.1
Standard I/O Mode Supported	Yes
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	NRKH.E239373
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document