


# CF211-03-03-02-1 Cut Sheet



igus continuous flexing control and signal cable, shielded, AWM, 3 twisted pairs, 22 AWG (0.34mm<sup>2</sup>), bare copper, TPE conductor insulation material, pair 1: white and brown, pair 2: green and yellow and pair 3: grey and pink, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF211-03-03-02-1>

## Technical Specifications

<b>Brand</b>	igus
<b>Item</b>	Cable
<b>Wire/Cable Type</b>	Control and signal
<b>UL Wire/Cable Type</b>	AWM
<b>Applicable Standards</b>	UL 2464
<b>Application</b>	General purpose
<b>Flexibility</b>	Continuous flexing
<b>Voltage Rating</b>	300V
<b>Conductors</b>	3 twisted pairs
<b>Conductor Size</b>	22 AWG (0.34mm <sup>2</sup> )
<b>Conductor Stranding</b>	42-stranded
<b>Conductor Material</b>	Bare copper
<b>Conductor Insulation Material</b>	TPE

<b>Conductor Insulation Color</b>	Pair 1: white and brown, pair 2: green and yellow and pair 3: grey and pink
<b>Shielding</b>	Shielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Gray
<b>Nominal Overall Cable Diameter</b>	0.315in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	1 to 75ft = Coil, 76 to 390ft = 14 x 7in Reel, 391 to 560ft = 14 x 10in Reel, 561 to 870ft = 16 x 10in Reel, 871 to 1230ft = 18 x 10in Reel, 1231 to 1590ft = 18 x 13in Reel, 1591 to 1615ft = 24 x 17in Wooden Reel

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E310776
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>