


CF211-P-02-01-02-1 Cut Sheet



igus continuous flexing control and signal cable, shielded, AWM, 1 twisted pair, 24 AWG (0.25mm²), bare copper, TPE conductor insulation material, white and brown, PUR jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF211-P-02-01-02-1>

Technical Specifications

Brand	igus
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	AWM
Applicable Standards	UL 20233
Application	General purpose
Flexibility	Continuous flexing
Voltage Rating	300V
Conductors	1 twisted pair
Conductor Size	24 AWG (0.25mm ²)
Conductor Stranding	32-stranded
Conductor Material	Bare copper
Conductor Insulation Material	TPE

Conductor Insulation Color	White and brown
Shielding	Shielded
Jacket Material	PUR
Jacket Color	Gray
Nominal Overall Cable Diameter	0.197in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 924ft = 14 x 7in Reel, 925 to 1010ft = 14 x 10in Reel, 1011 to 1443ft = 16 x 10in Reel, 1444 to 1615ft = 18 x 10in Reel

Agency Approvals

UL Listed File #	None
UL Recognized File #	E310776
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document