


# CF211-P-02-04-02-1 Cut Sheet



igus continuous flexing control and signal cable, shielded, 4 twisted pairs, 24 AWG (0.25mm<sup>2</sup>), 32-stranded, bare copper, TPE conductor insulation material, PUR jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF211-P-02-04-02-1>

## Technical Specifications

<b>Brand</b>	igus
<b>Item</b>	Cable
<b>Wire/Cable Type</b>	Control and signal
<b>UL Wire/Cable Type</b>	AWM
<b>Applicable Standards</b>	UL 20233
<b>Application</b>	General purpose
<b>Flexibility</b>	Continuous flexing
<b>Voltage Rating</b>	300V
<b>Conductors</b>	4 twisted pairs
<b>Conductor Size</b>	24 AWG (0.25mm <sup>2</sup> )
<b>Conductor Stranding</b>	32-stranded
<b>Conductor Material</b>	Bare copper
<b>Conductor Insulation Material</b>	TPE

<b>Conductor Insulation Color</b>	Pair 1: white and brown, pair 2: green and yellow, pair 3: grey and pink and pair 4: blue and red
<b>Shielding</b>	Shielded
<b>Jacket Material</b>	PUR
<b>Jacket Color</b>	Gray
<b>Nominal Overall Cable Diameter</b>	0.295in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 20 to 99ft = Coil</li><li>• 100 to 450ft = 14 x 7in Reel</li><li>• 451 to 640ft = 14 x 10in Reel</li><li>• 641 to 980ft = 16 x 10in Reel</li><li>• 981 to 1370ft = 18 x 10in Reel</li><li>• 1371 to 1500ft = 18 x 13in Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E310776
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>