

CFW320A07P3S2NB20 Cut Sheet



WEG Electric CFW320 series AC general purpose drive, enclosed, 230 VAC, 2hp with 1-phase input, SVC, V/Hz or VVW mode, A frame. Optional communication and I/O modules available.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CFW320A07P3S2NB20>

Technical Specifications

| | |
|--|---|
| Brand | WEG Electric |
| Item | Drive |
| Controller Type | General purpose |
| Series | CFW320 |
| Voltage Type | AC |
| Nominal Drive Input Voltage | 230 VAC |
| Nominal Drive Output Voltage | 230 VAC |
| Number of Input Phases | 1 |
| Number of Output Phases | 3 |
| Horsepower By Input Phase | 2hp with 1-phase input |
| Amperage Rating | 7.3A |
| Control Mode | SVC, V/Hz or VVW |
| Safe Torque Off (STO) | No |
| Temperature Rating | 0 to 50 deg C |
| Enclosure Type | Enclosed |
| IP Rating | IP20 |
| Mounting | 35mm DIN rail, panel or wall |
| Frame Size | A |
| Input Signal | 4-20 mA, voltage or potentiometer input |
| Output Type | PWM output |
| Reverse Capability | Built-in |
| Internally Bypassed | No |
| Carrier Frequency Range | 2.5-15 kHz |
| Output Frequency Range | 0.1-400 Hz |
| Number of Analog Input Channels | 1 |
| Number Of Input Channels | 1 |
| Analog Input Signal Type | Current/voltage |
| Number of Non-Isolated Analog Input Commons | 1 |
| Number of Points per Analog Input Common | 1 |

| | |
|--|--|
| Input Resolution | 10-bit |
| Input Current Signal Range | 4-20 mA |
| Input Voltage Signal Range | 0-10 VDC |
| Number of Discrete Input Points | 4 |
| Nominal Discrete Input Voltage | 24 VDC |
| Discrete Input Type | Sinking/sourcing |
| Number of Non-Isolated Discrete Input Commons | 1 |
| Number of Points per Discrete Input Common | 4 |
| Number of Discrete Output Points | 1 |
| Nominal Discrete Output Voltage | 250 VAC |
| Discrete Output Type | Relay |
| Relay Configuration | (1) Form C (SPDT) relay |
| Number of Isolated Discrete Output Commons | 1 |
| Number of Points per Discrete Output Common | 1 |
| Load Current | 0.5A/point |
| Fuse Type | User-supplied external fuse |
| Programming Language | Ladder |
| SCCR Rating | 65kA SCCR |
| Connector Type | Screw terminals |
| For Use With | 3-phase induction motors |
| Additional Information | Optional communication and I/O modules available |

CFW320A07P3S2NB20 Cut Sheet

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E184430 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CFW320A07P3S2NB20.pdf>
See store item page for other formats.