


CTS16 Cut Sheet



MK Morse hole cutter, 1in (25mm), carbide tipped steel, straight pitch, 3/16in (4.5mm) maximum cutting depth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CTS16>

Technical Specifications

Brand	MK Morse	Toothing	Straight pitch
Item	Hole cutter	Cutting Direction	Right hand
Hole Saw Size	1in (25mm)	For Use On	Steel, stainless steel, aluminum, wood, plastic and composite
Maximum Cutting Depth	3/16in (4.5mm)	Application	Hole cutting
Material	Carbide tipped steel	Additional Information	Integrated ejector spring for quick slug removal
Hardened Steel Backer	No		
Tooth Density	3 teeth/in		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement