

CTS48 Cut Sheet



MK Morse hole cutter, 3in (76mm), carbide tipped steel, straight pitch, 3/16in (4.5mm) maximum cutting depth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CTS48>

Technical Specifications

Brand	MK Morse
Item	Hole cutter
Hole Saw Size	3in (76mm)
Maximum Cutting Depth	3/16in (4.5mm)
Material	Carbide tipped steel
Hardened Steel Backer	No
Tooth Density	3 teeth/in

Toothing	Straight pitch
Cutting Direction	Right hand
For Use On	Steel, stainless steel, aluminum, wood, plastic and composite
Application	Hole cutting
Additional Information	Integrated ejector spring for quick slug removal

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement