

D80-0P-4T Cut Sheet



ProSense inductive proximity sensor, rectangular, 80 x 40 x 105mm body, polyphenylene ether housing, PNP, N.O./N.C. selectable output, 20-60mm sensing distance, non-flush, 100 Hz switching frequency, IP65, terminal chamber.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D80-0P-4T>

Technical Specifications

Brand	ProSense
Item	Proximity sensor
Sensor Type	Inductive
Application	Standard duty and long range
Shape	Rectangular
Housing Size	80 x 40 x 105mm body
Housing Material	Polyphenylene ether
Sensing Method	Extended sensing
Adjustable	Yes
Number of Wires	3
Switching Output	PNP
Operation Mode	N.O./N.C. selectable output

Sensing Distance	20-60mm
Mounting Type	Non-flush
IO-Link Compatible	No
Switching Frequency	100 Hz
Operating Voltage	10-36 VDC
Operating Temperature	-25 to 80 deg C
Weld Field Immune	No
Chip Immune	No
IP Rating	IP65
Connection	Terminal chamber
Conductor Size	2.50 mm ² (14 AWG)

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/D80-0P-4T.pdf>
See store item page for other formats.